

KEY
PRODUCTS
FOR YOUR
INDUSTRY

Lab Equipment & Instrumentation for your Industry

Discover key items for daily lab analysis from temperature control to cold storage, including balances, hotplates and stirrers, and electrochemistry

 **BINDER**

Best conditions for your success

Model VD 23 Vacuum Drying Chamber for Non-Flammable Solvents, 23L

Temperature Range: Ambient +15°C to 200°C;

Light: No Lighting.

- Patented expansion shelf technology ensures optimal heat transfer
- Direct heat transfer through large thermal conducting plates
- Coordinated modular system with vacuum pump and vacuum module
- Shelves easy to position
- Inner chamber of oven easy to clean

Cat. No	Description	Pack qty
15632186	Model VD 23 Vacuum Drying Chamber for Non-Flammable Solvents, 23 L	1

Buy Now



Find it at:
www.eu.fishersci.com/go/industryinstrumentation

 **fisher scientific**
part of Thermo Fisher Scientific



Safe 2020 Class II Biological Safety Cabinets

Protect samples in research labs, pharmaceutical quality control labs, pharmacies, and clinics with Thermo Scientific™ Safe 2020 Class II Biological Safety Cabinets.

- Superior personnel and product protection with best-in-class air flow and filter technology
- Exceptionally comfortable ergonomic design prevents user fatigue and promotes safe working habits
- Maximised energy efficiency for environmental protection and significant cost savings

Cat. No	Description	Pack qty
10462614	Safe 2020 Class II Biological Safety Cabinets	1

[Buy Now](#)

16 Centrifuge Series

The Thermo Scientific™ Heraeus Megafuge 16 general purpose centrifuge series is ideal for everyday sample processing, including clinical protocols, cell culture applications and microplate processing. The refrigerated version is designed for handling temperature sensitive sample processing between -10° and +40°C.

- Secure locking system allows easy push-button installation and exchange of rotors
- Saves time switching between applications



Cat. No	Description	Pack qty
10596614	16 Centrifuge Series	1

[Buy Now](#)

ST 16 Centrifuge Series

The Thermo Scientific™ Sorvall™ ST 16 general purpose centrifuge series is perfect for everyday sample processing, including clinical protocols, cell culture applications and microplate processing. The refrigerated version is ideal for handling temperature sensitive sample processing between -10° and +40°C.

- Secure locking system allows easy push-button installation and exchange of rotors
- Saves time switching between applications



Cat. No	Description	Pack qty
10688725	ST 16 Zentrifugenserie	1

[Buy Now](#)

Under Bench, Spark Free Interior, Lab Fridge

For secure, accurate and long lasting fridge storage of temperature sensitive products, the Liebherr™ Under Bench, Spark Free Interior, Lab Fridge is fully equipped for lab applications with Liebherr build quality you can rely on.

- Table height spark free lab fridge, reach in, 1 section, width 600mm, gross capacity 141 L.

Cat. No	Description	Pack qty
10729575	Under-Bench, Spark-Free Interior, Lab Fridge	1

[Buy Now](#)



Class II Biological Safety Cabinets

Conserve energy with these cabinets, which combine smart design and extraordinary value with best in class energy efficiency, reliability and usability.

- Available in 90cm, 120cm, 150cm and 180cm
- With microprocessor control

Cat. No	Description	Pack qty
10795194	Class II Biological Safety Cabinets	1

[Buy Now](#)

Benchtop pH/Ion Meter

Precise electrochemical measurement combined with flexibility, innovative design and ease of use. Mettler Toledo™ S220 SevenCompact™ pH/Ion Benchtop Meter measures ORP and ion concentration in various units and is suitable for a wide range of applications.

- User friendly design: colour display, intuitive icons and menu settings in 10 languages

Cat. No	Description	Pack qty
11374233	S220 SevenCompact™ pH/Ion Meter	1

[Buy Now](#)





FB70155 Pump

Oil-free piston pump. Fisherbrand™ FB70155 Pump designed for general duty laboratory applications requiring only rough vacuum or moderate pressure.

- Tough, lightweight, plastic housing with integral carrying handle
- Water jet or aspirator replacement for general duties
- Lightweight, compact, portable, standard-duty operation

Cat. No	Description	Pack qty
11533485	FB70155 Pump	1

[Buy Now](#)

fisherbrand

Immersion Circulator

Includes fixing clip. Fisherbrand™ Polystat™ Immersion Circulator is DIN 12876-1 certified.

- Temperature range of 20 to 150°C
- Electrical requirements: 230V, 50Hz, 9A
- Includes wall fixing clip
- Flow rate of 15L/min
- Weight: 4.1kg
- Temperature stability of $\pm 0.03^\circ\text{C}$

Cat. No	Description	Pack qty
11930228	Immersion Circulator	1

[Buy Now](#)


SARTORIUS

Analytical Weighing Balances

Offers smart and efficient weighing, improved workflows with touchscreen and scroll technology which enables users to easily navigate through all balance operations.

- Simple menu navigation and integrated applications at the touch of a key
- Clearly visible icons provide easy-to-follow balance operations; displayed results give users immediate feedback and confidence
- Maximum accuracy all the time, thanks to isoCAL™ fully automatic internal calibration and balance adjustment



Cat. No	Description	Pack qty
13502980	Analytical Weighing Balances	1

[Buy Now](#)



Hot Plate Stirrer, 310°C, Aluminium Alloy

Incorporates extra technology including a powerful motor for a higher range of speeds and additional temperature control mode for faster heating of medium.

- Integrated temperature control
- Includes PT 1000 temperature sensor (PT 1000.60)
- Exact temperature and speed setting via digital display, even when switched off

Cat. No	Description	Pack qty
10414452	RCT Hot Plate Stirrer, Ambient to 310°C, Aluminum Alloy	1

[Buy Now](#)



KISS E Immersion Circulator

Immersion thermostats are suitable for controlling the temperature of any bath as the screw clamp allows the thermostats to be easily mounted on different vessels.

- Minus temperatures are achieved in combination with refrigerated bath or immersion cooler
- Fitted with overtemperature and low level protection suitable for Safety Class III/FL (DIN 12876)



Cat. No	Description	Pack qty
15682707	KISS E Immersion Circulator	1

[Buy Now](#)



TSX Series Ultra-Low Freezers

Thermo Scientific™ TSX Series ultra-low freezers are designed to meet the highest sustainability, temperature management and reliability standards for -80°C and -70°C storage.

- No need to worry about where your samples are stored within the freezer. With peak variation less than 5°C, your samples are protected and safely stored throughout the entire cabinet space.
- Long warm-up time from -50°C to -80°C: 5.05 hours

Cat. No	Description	Pack qty
15788587	TSX Series Ultra-Low Freezers	1

[Buy Now](#)



40/50 Vis/UV-Vis Spectrophotometers



The Thermo Scientific™ GENESYS™ 50 is a dual beam UV-Vis spectrophotometer in a single-cell configuration that meets all of the specifications for critical quality control applications and precise chemical measurements.

- 7-inch high-resolution touchscreen user interface
- Local control for speed and reliability
- Networking capable (Wi-Fi adaptor available)
- Large sample compartment with front access

Cat. No	Description	Pack qty
15899991	40/50 VIS- und UV/VIS-Spektralphotometer	1

[Buy Now](#)



Best conditions for your success

Series UF V Ultra Low Temperature Freezers

Series UF V Ultra Low Temperature Freezers combine environmental friendliness with low energy consumption, convenient operation and an individual safety concept.

- Lowest energy consumption in its class
- Powerful cascade compressor cooling unit
- Environmentally friendly refrigerants R-290 and R-170
- Flow Rate of 15L/min
- Weight: 4.1kg
- Temperature Stability of $\pm 0.03^{\circ}\text{C}$

Cat. No	Description	Pack qty
15901102	Series UF V Ultra Low Temperature Freezers	1

[Buy Now](#)



ECO Clean Bench Floor Stands

Due to DC motors, Thermo Scientific™ Heraguard™ clean benches use less energy to operate so there is less heat emitted into the lab than traditional AC motor clean benches. Based on data from internal testing and The University of Michigan Field Study, published in American Biotechnology Laboratory.



Cat. No	Description	Pack qty
10294014	ECO Clean Bench Floor Stands	1

[Buy Now](#)




UV LIGHT OPTION, FACTORY INSTALLED

Immersion thermostats are suitable for controlling the temperature of any bath as the screw clamp allows the thermostats to be easily mounted on different vessels.

- Minus temperatures are achieved in combination with refrigerated bath or immersion cooler
- Fitted with overtemperature and low level protection suitable for Safety Class III/FL (DIN 12876)
- Can be used for externally attached applications using pump connections at rear

Cat. No	Description	Pack qty
10019982	UV LIGHT OPTION, FACTORY INSTALLED	1


[Buy Now](#)



Help & Support Center

Fisher Scientific website How-To Videos & FAQs

[Explore Now >](#)





PTFE Diaphragm Vacuum Pump

Use these chemically resistant pumps for applications involving aggressive solvents and acidic vapours.

- Chemically resistant, ideal for applications involving aggressive solvents and acidic vapours
- Replacement for rotary vane pumps and water aspirators, especially in rough vacuum applications where corrosive vapours are encountered
- Pump heads are made from PTFE with carbon fibre reinforcing to handle corrosive and aggressive vapours without damage

Cat. No	Description	Pack qty
12981131	Polytetrafluoroethylene Diaphragm Vacuum Pump	1

Buy Now

AREX Hot Plate Stirrer with VTF, 370°C, Aluminium

Stirring Range: 1500 rpm; Size: 6.1 in. dia.

- Outstanding temp. uniformity with CerAlTop™ aluminium alloy heating plate
- Excellent resistance to chemicals, scratches and surface abrasions
- Maximum temperature 370 °C
- Accepts up to 20 litre flasks



Cat. No	Description	Pack qty
15369244	AREX Hot Plate Stirrer with VTF, 370°C, Aluminum	1

Buy Now



Set Your Lab in Motion

Maximise your time and budget while getting the supplies you need

COVID-19 IMPACTED LABS ELIGIBLE
Deadline to apply 31st August 2020

Contact us today:

Austria: fishersci.at Belgium: fishersci.be Denmark: fishersci.dk
 Germany: fishersci.de Ireland: fishersci.ie Italy: fishersci.it
 Finland: fishersci.fi France: fishersci.fr Netherlands: fishersci.nl
 Norway: fishersci.no Portugal: fishersci.pt Spain: fishersci.es
 Sweden: fishersci.se Switzerland: fishersci.ch UK: fishersci.co.uk